AM LEONARD SPRAY MAX SPRAYERS – FLOW RATES

Soft Flow Technology provides the answer, creating that constant output application rate throughout your treatment process, unlike Hand Pump Applicators. Our Soft Flow rates of application provide the gentle flow needed to treat cracks and cervices in all types of structures where insects live. Match Soft Flow to your spray tip of choice and experience a day's work without Hand Pumping. You will never go back.

opproximate value	and flow settings:	
Run Times – contir	uous use	
ow Flow – 4 hours 60 PSI Closed Trigg		
High Flow – 1.5 hou 70 PSI Closed Trigg		
ow Flow Setting a	nd Tips	
Fan Spray Tip Fip 8001 Fip 8002	400mls/min 14oz 620mls/min 21oz	
Pin and Cone Spray	Тір	
	500mls/min 17oz 235mls/min 8oz	
High Flow Setting	nd Tips	
Pin and Cone Spray Fip 08 Pin/Cone	•	
an Spray Tip Tip 8002	920mls/min 32oz	